

Glass basket 500x500mm - maximum glass height 110 mm - with blue 5x5 compartment division - maximum glass diameter 90mm





Product specifications

External dimensions (L x W x H)	500 × 500 × 149 mm
Color	Grey
Material	PP
Bottom	Open and extra reinforced, making it suitable for high loads and for use in basket transport machines with transport hooks.
Sidewalls	Open, for optimal washing results and a faster drying process
Handles	4-sided - open, for added wearing comfort
European Article Number	7424901366387
Maximum glass height	110
Maximum Ø glass	90
Internal dimensions (L x W x H)	465 × 465 × 110 mm

Properties

Our baskets guarantee safe transport and efficient storage of your glassware and tableware.

The open design of the basket ensures optimal washing results.

Determine the appropriate basket layout and height easily with the size chart. Request a size chart by calling or filling out our contact form.

The basket has 4-sided receptacles for color clips (see accessories).

Color clips can be clicked into the basket on all four sides, for example, to indicate contents.

Suitable for use in basket transport machines with transport hooks.



Transoplast +31(0)314 66 44 00 website@transoplast.com dev.transoplast.com


Description

The glass basket 50.NK.110.115145.5x5 consists of a gray base basket with a blue 5x5 compartment division and a low top edge without compartment division - maximum glass diameter Ø90mm.

The glass basket with dimensions 500 x 500 has an inner height of 110 mm. Glasses with a height of up to 110 mm can fit in this basket. Thanks to the open basket construction, washing water and drying air have very good access to glassware and porcelain. The dishwasher baskets thus achieve an optimal washing result and a faster drying process. The bottom is additionally reinforced, allowing the basket to rotate in a basket transport machine with transport hooks. Transoplast's glass basket is exceptionally durable and has the best references in the market.



Alternatieve artikelen





Transoplast +31(0)314 66 44 00 website@transoplast.com dev.transoplast.com