

# Glass basket 500x500mm - maximum glass height 225 mm - with yellow 4x4 compartment division - maximum glass diameter 113mm



### **Product specifications**

External dimensions ( L x W x H)	500 × 500 × 265 mm
Color	Grey
Material	PP
Bottom	Open and extra reinforced, making it suitable for high loads and for use in basket transport machines with transport hooks.
Sidewalls	Open, for optimal washing results and a faster drying process
Handles	4-sided - open, for added wearing comfort
European Article Number	7424901366387
Maximum glass height	225
Maximum Ø glass	113
Internal dimensions (L x W x H)	465 × 465 × 225 mm

### Properties

Our baskets guarantee safe transport and efficient storage of your glassware and tableware.

The open design of the basket ensures optimal washing results.

Determine the appropriate basket layout and height easily with the size chart. Request a size chart by calling or filling out our contact form.

The basket has 4-sided receptacles for color clips (see accessories).

Color clips can be clicked into the basket on all four sides, for example, to indicate contents.

Suitable for use in basket transport machines with transport hooks.



#### Transoplast +31(0)314 66 44 00 website@transoplast.com dev.transoplast.com


## Description

The glass basket 50.NKG.121.200230.4X4L consists of a gray base basket with a yellow compartment division 4x4 - maximum glass diameter Ø113mm.

The glass basket with dimensions 500 x 500 has an inner height of 120 mm. Glasses with a height of up to 120 mm can fit in this basket. Thanks to the open basket construction, washing water and drying air have very good access to glassware and porcelain. The dishwasher baskets thus achieve an optimal washing result and a faster drying process. The bottom is additionally reinforced, allowing the basket to rotate in a basket transport machine with transport hooks. Transoplast's glass baskets are exceptionally durable and have the best references in the market.



### Alternatieve artikelen





Transoplast +31(0)314 66 44 00 website@transoplast.com dev.transoplast.com