

Glass crate BASIC - 600 x 400 x H 154 mm for 12 glasses - max. height 125 mm - max. Ø 116 mm - single compartment





Transoplast +31(0)314 66 44 00 website@transoplast.com dev.transoplast.com

Product specifications

Weight (kg)	1,9 kg
External dimensions (L x W x H)	600 × 400 × 154 mm
Temperature range	-40°C to +70°C
Capacity	29.3 liter
Material	HDPE
Bottom	Perforated, reinforced
Sidewalls	Perforated
Handles	Open (four openings)
European Article Number	7424901192108
Maximum glass height	125
Maximum Ø glass	116
Internal dimensions (L x W x H)	568 × 368 × 140 mm

Properties

Attention before ordering!

Glass dimensions are crucial when choosing the crate. Measure the height and diameter at the widest point.

Plastic glass crate for rinsing, storing, and transporting 12 glasses or cups. This crate is suitable for glassware and tableware with a maximum height of 125 mm and maximum Ø 116 mm. The glass size is essential when selecting the crate. If the glass is taller than 125 mm or much narrower than Ø 116 mm, this crate is not suitable. Please check our other glass crates in this series.

The glass crate is 600 x 400 mm and 130 mm high, with a single compartment division of 12 sections. Each glass has its own compartment and they do not touch each other. This crate is equipped with a single compartment division and is therefore suitable for cups and tumbler glasses. If you want to transport fragile glassware with a base in this crate, we recommend the glass crate with a double compartment division (item number 30.115.3x4.O+B). The most fragile part of the glass, the base, is better protected against breakage in a crate with upper and lower compartment divisions. The glassware is safely cleaned, stored, and transported thanks to the compartment division. The coarse perforated side walls and bottom allow good access for rinse water and cleaning agents, resulting in a clean wash. The glass crates have a Euro norm size and are therefore perfect to combine with other plate bins and stacking crates with Euro norm dimensions. Moreover, the glass crates can be stacked without loss of space on standardized supports, roll containers, and pallets. For more information, please contact our product advisors.

Description

Please note before ordering!

The glass dimensions are crucial when choosing the crate. Measure the height of the glass

and the diameter at its widest point.

Plastic glass crate for rinsing, storing, and transporting 12 glasses or cups. This crate is suitable for glassware and tableware with a maximum height of 125mm and a maximum Ø of 116mm. The glass size is paramount when selecting the crate. If the glass is higher than 125mm or much narrower than Ø 116mm, then this crate is not suitable. Please check our other glass crates in this series. The glass crate, measuring 600 x 400mm, is 130mm high and has a single compartment division of 12 sections. Thanks to this division, each glass has its own unit, preventing contact with other glasses. This crate is equipped with a single compartment division and is suitable for cups and tumbler glasses. If you intend to transport fragile glassware with a base in this crate, we recommend the glass crate with a double compartment division (item number 30.115.3x4.O+B). The most delicate part of the glass, the base, is better protected against breakage in a crate with both upper and lower compartment divisions. The glassware is safely cleaned, stored, and transported thanks to the contents, ensuring a clean washing result. The glass crates are Euronorm-sized, allowing for perfect compatibility with other plate bins and stacking crates with Euronorm dimensions. Moreover, the glass crates can be stacked without space loss on standardized supports, roll containers, and pallets. For further information, please contact our product advisors.





Transoplast +31(0)314 66 44 00 website@transoplast.com dev.transoplast.com

Matching accessories











52.TR6040.4.H

52.TR6040.4.L

2800.510.312



Transoplast +31(0)314 66 44 00 website@transoplast.com dev.transoplast.com